






POLISHING CLOTH GUIDE

	NAME	COMPOSITION	ABRASIVE	APPLICATION
	FLAT	woven acetate	diamond 9 μ /3 μ	fine grinding and pre-polishing of Ferrous metals, non ferrous metals, coatings and plastics
	FAST	woven acetate	diamond 6 μ /1 μ	Universal pre-polishing of all Materials
	FAP	synthetic nap	diamond 3 μ /1 μ alumina < 3 μ	Final polishing of all materials
	FLUX	synthetic nap	diamond 3 μ /1 μ alumina < 3 μ	Final polishing for sintered carbides and steels
	KEMO	neoprene	colloidal silica alumina < 1 μ	Chemo-mechanical polishing of all oxide slurries $\leq 1\mu$ materials, recommended as a final diamond $\leq 1\mu$ polishing step of non ferrous materials
	MIX	tnt	diamond 6 μ /1 μ	Final polishing of materials



HOW TO REACH US



Represented by:



G&G SURFACE TECHNOLOGY

Via Leonardo da Vinci, 6
27040 BOSNASCO (PV) - ITALY

T +39 0385 272022

F +39 0385 272606

info@gegindustry.com

www.gegindustry.com